

	Hygienic Rail		Magnetic Rail	Pipe Rail			
	T021	T022	Henry T200	T280	T290		
Installation Location / Temperature Range							
Operating Room		X	X				
Cold Room (0°C to +8°C)		X		X			
Freezer Room (0°C to -28°C)	X				X		
Dimensions [mm]							
Max. Width (Clear Width)	3400	3400	1330	4500	4500		
Max. Height (Clear Height)	3800	3800	2800	4500	4500		
Min. Width (Clear Width)	700	700	400	1000	1000		
Min. Height (Clear Height)	1000	1000	1000	1800	1800		
PU Thickness	120	80	40	80	120		
Double-Leaf Variant	T023	T023	T202				
Max. Leaf Weight	120 kg	120 kg	80 kg	300 kg	300 kg		

Motorization Optional	X	X		X	X		
Magnetic Rail Optional			X				
Material							
Stainless Steel	V2A (1.4301), V4A (1.4404) circular matt, brushed, stripe matt, linen (1.4016)						
Galvanized Steel (Painted)	RAL9002, RAL9005, RAL9010, RAL7016, RAL7035						
Other RAL Colors on Request	X						
Frame							
Installation in Masonry	Flat Frame, Clamping Frame, Surround Frame, Corner Frame	Flat Frame, Clamping Frame, Surround Frame, Corner Frame	Flat Frame (150×50)				

Installation in Element (Panels)	Foamed Stock (500), Clamping Frame	Clamping Frame					
Threshold	Available optionally						
Handle Options							
Press Lever	X	X		X	X		
Handle Tube	X	X	X	X	X		
Various Versions							
Special Equipment							
Rail Passage		X		X			